



ALPHA

Advanced Stereo Zoom Microscope for inspection and material rework

- Wide range of magnification x2.1 - x160
- Patented stereo Expanded-Pupil optical technology provides superb resolution and contrast
- Easy hand-to-eye coordination resulting in increased throughput, accuracy and reduced scrap
- Stereo optics for easy viewing and documenting of complex surfaces

Alpha utilises Vision Engineering's patented ISIS Expanded-Pupil technology to provide up to 10 times greater freedom of head movement than conventional binocular eyepiece microscopes.

The Expanded-Pupil optics of Alpha significantly increases head freedom and eye-relief compared to conventional eyepiece microscopes, reducing operator stress and fatigue over long periods of time. High precision optics provide maximum brilliance with high contrast images.

Alpha is used in a wide range of both industrial and life science applications, ranging from general manufacturing, medical devices, electronics, precision engineering, plastics and rubber to intricate life science work. The multiple accessories available for Alpha enable a wide variety of tasks including inspection, manipulation, assembly, dissection, soldering, polishing and finishing.

Features and Benefits

- Incorporated modern advances in optical design allow eyes and hands to work together resulting in increased throughput, accuracy and reduced scrap and rework.
- Wide magnification range of x2.1 - x160 provides clear, sharp images with long working distances and large depth of field.

Speed

- Increased head and body freedom for the operator leads to greater productivity, improved quality control and reduced fatigue.

Versatility

- Modular design allows for quick changeover of accessories and options. For example, from manipulation to high magnification inspection on to image capture.

Ergonomics

- Patented Expanded-Pupil technology expands the exit pupil providing head freedom and eye-relief for excellent ergonomics, superb hand-to-eye coordination and the ability to wear glasses, if required.



Alpha bench stand with optional oblique and direct viewer.

Stand Options

- Stable, focusable bench stand with subject holder, substage illumination and floating or measuring stage options.
- Adjustable, swing away boom mount for mounting directly to user's work surface or with coated platform base for easy transport.

Crank handle option allows convenient vertical adjustment when frequent changes in working distance are required.



Alpha boom mount with optional fixed angle viewer.

Technical Data

Optical

- Afocal stereo zoom Expanded-Pupil microscope provides a 26.4° field angle.
- Expanded-Pupil patented technology optimises head and body freedom providing 10 times greater head freedom than conventional binocular eyepiece microscopes.

Zoom Magnification (see table below)

- x7 - x40 multiplied by combinations of objective lenses and multipliers (total zoom magnification range x2.1 - x160).
- Zoom ratio 5.7:1
- Secondary multipliers x1.5 and x2.0
- Reducing objectives to increase working distance and field of view.
- Magnifying objectives to increase total magnification.

Illumination

- 12V/60W semi-coaxial long-life spotlamps.
- 14 point LED ring light with intensity control (optional).
- Substage illumination (bench stand only) 12V/20W Halogen lamp.
- Option of tilting substage illuminator to enhance contrast.

Alpha UV / White Light

Alpha UV / White Light is ideal for a wide range of non-destructive testing, crack & fatigue detection, conformal coating inspection of PCB's, UV medical adhesives and general UV inspection tasks.



- Superb stereo vision gives unsurpassed crack and coating visibility.
- Fast & accurate fault detection.
- Enhanced productivity and reduced scrap rates.

Fault detection is made more effective by magnification, highlighting minute cracks and pitting. Alternate UV / white light inspection can be selected with a footswitch allowing the inspector hands-free component manipulation.

Objective Lens	Zoom Range			Working Distance	Field of View at Max. Zoom			Field of View at Min. Zoom		
		with x1.5 multiplier	with x2.0 multiplier			with x1.5 multiplier	with x2.0 multiplier		with x1.5 multiplier	with x2.0 multiplier
x0.3*	x2.1 – x12	x3.2 – x18	x4.2 – x24	312mm	14.5mm	9.7mm	7.2mm	82.6mm	55.0mm	41.3mm
x0.5	x3.5 – x20	x5.3 – x30	x7.0 – x40	177mm	8.9mm	5.9mm	4.5mm	51.0mm	34.0mm	25.5mm
x0.7	x4.9 – x28	x7.4 – x42	x9.8 – x56	130mm	6.4mm	4.3mm	3.2mm	36.0mm	24.0mm	18.0mm
x1.0	x7.0 – x40	x10.5 – x60	x14 – x80	85mm	4.4mm	2.9mm	2.2mm	24.9mm	16.6mm	12.5mm
x1.5	x10.5 – x60	x15.8 – x90	x21 – x120	47mm	3.0mm	2.0mm	1.5mm	17.0mm	11.3mm	8.5mm
x2.0	x14 – x80	x21 – x120	x28 – x160	29mm	2.2mm	1.5mm	1.1mm	12.6mm	8.4mm	6.3mm

* when using the x0.3 objective lens with a bench stand model, an extended stand column is required to accommodate the increased working distance.

Accessories

Oblique and Direct Viewer

- Allows the operator to view a subject from an angle of 34° from vertical, which can be rotated through to 360° enabling a better stereo view of 3-dimensional subjects including PCB solder joints, holes, pillars and thread forms. Both manual and motorised versions are available.



Oblique and direct viewer



Fixed angle viewer

Fixed Angle Viewer

- Allows the user three options; a fixed angle of 25° from vertical, the ability to view vertically or tilting the optical head and using the system standing up.

Ergowedge

- Allows the view to be adjusted between -5° and -25° from horizontal.



Ergowedge

Image Capture and Archive

- Digital, USB and 35mm SLR cameras including Sony, Nikon, Pixera, Canon and other leading makes.
- Modular multimedia solutions for image archiving, acquisition, processing, analysis and documentation.



Image capture and archive

Step Magnification Multiplier


- Allows the stereo zoom range to be increased by a factor of x1.5 or x2 without any loss in working distance.



Step magnification multiplier

Measuring/Comparison Graticule

- Allows the user the ability to measure and compare against a scale. Standard range is available as a crossline or graduated scale. Custom graticules can be manufactured to specific designs.



Alpha Bench Stand

Bench Stand:


- A = 390mm
- B = 150mm
- C = 234mm
- D = 127mm
- E = 490mm

Unpacked weight: 12.0kg
Packed weight: 14.0kg

Boom Mount:

- F = 400mm maximum
- G = 310mm less working distance
- H = 440mm

Unpacked weight: 19.0kg
Packed weight: 22.0kg



Alpha Boom Mount

For more information...

Vision Engineering has a network of offices and technical distributors around the world. For more information, please contact your Vision Engineering branch, local authorised distributor, or visit our website.

Vision Engineering Ltd.
(Manufacturing)
Send Road, Send, Woking,
Surrey, GU23 7ER, England
Tel: +44 (0) 1483 248300
Fax: +44 (0) 1483 223297
Email: generalinfo@visioneng.com

Vision Engineering Inc.
(Manufacturing & Commercial)
570 Danbury Road, New Milford,
CT 06776 USA
Tel: +1 (860) 355 3776
Fax: +1 (860) 355 0712
Email: info@visioneng.com

Vision Engineering Ltd.
(Central Europe)
Anton-Pendele-Str. 3,
D-82275, Emmering, Germany
Tel: +49 (0) 8141 40167-0
Fax: +49 (0) 8141 40167-55
Email: info@visioneng.de

Vision Engineering Ltd.
(France)
ZAC de la Tremblaie, Av. de la Tremblaie
91220 Le Plessis Paté, France
Tél: +33 (0) 160 76 60 00
Fax: +33 (0) 160 76 60 01
Email: info@visioneng.fr

Vision Engineering Ltd.
(Commercial)
Monument House, Monument Way West,
Woking, Surrey, GU21 5EN, England
Tel: +44 (0) 1483 248300
Fax: +44 (0) 1483 248301
Email: generalinfo@visioneng.com

Vision Engineering Inc.
(Commercial West Coast USA)
745 West Taft Avenue, Orange,
CA 92865 USA
Tel: +1 (714) 974 6966
Fax: +1 (714) 974 7266
Email: info@visioneng.com

Nippon Vision Engineering
(Japan)
272-2 Saedo-cho, Tsuduki-ku,
Yokohama-shi, 224-0054, Japan
Tel: +81 (0) 45 935 1117
Fax: +81 (0) 45 935 1177
Email: info@visioneng.jp

Vision Engineering Ltd.
(Italy)
Via Cesare Cantù, 9
20092 Cinisello Balsamo MI, Italy
Tel: +39 02 6129 3518
Fax: +39 02 6129 3526
Email: info@visioneng.it

Distributor:

AMTECH spol. s r.o.
Banskobystrická 141, 621 00 Brno
Kancelář : Palackého tř. 153b, 621 00 Brno
tel.: +420 541 225 215 fax:+420 541 228 285
email: amtech@amtech.cz
www.amtech.cz



Visit our multi-lingual website:

www.visioneng.com