Off-cut Remover HEKTOR 2



Hektor separates milled PCBs carefully and fast. The off-cut material is removed smoothly and precisely. The matrix consists of two parts. This ensures easy and cost-saving change of the blades. Compressed air is used for the separation process. The operating pressure can be set on the machine. When the foot switch is pressed, the off-cut is punched out. The off-cuts are collected in the collecting box. When the gate is opened the waste material can be extracted.

Safe Operation

The PCB is slipped with its milled groove over the blade and is placed onto the matrix. The off-cut is pulled under the blade. When the foot switch is pressed, the off-cut is punched out and the waste material is collected inside the machine.

Technical Data				
Separation type	Punch blade			
Operation	by hand			
PCB thickness	max. 2.5 mm			
Air connection	1/4"-plug-in coupler			
Operating pressure		typical 4 bar		
Temperature/	Operation	+ 5 - 40°C / 10 - 85%		
Humidity	Storage	+ 0 - 60°C / 20 - 80%		
not condensing	Transport	- 25 - 60°C / 20 - 80%		
Weight		2.7 kg		
Dimensions H x D x W		170 x 255 x 220 mm		
Approvals		CE, FCC class A		

Part No.	Description				
8932145	Off-cut Remover Hektor 2 (bur for blade)				
8932xxx	Blade separate to order				
Content of delivery	Off-cut Remover with air pressure regulator Foot switch Hexagon key 2 mm Hexagon key 4 mm Operation manual d/e				



Blades To ensure the blade will not be jammed in the PCB, the milled groove should be at least 0.15 mm wider as the blade.		Width of milled groove	Recomemded blade thickness	Length of blade	Length of cut	Free of compon. on solder side	Length of milled groove	Width of off-cut	
	Part No.		Α	В	С	D	E	F	G
	8932137.001	Messer 1.5 T	≥1.5	1.35	17.2	4.7	>19.0	>19.0	3.0
	8932138.001	Messer 2.0 T	≥2.0	1.85	17.2	5.2	>19.0	>19.0	3.0
	8932191.001	Messer 2.4 T	≥2.4	2.25	18.0	5.7	>19.0	>19.0	3.0
	8932139.001	Messer 2.5 T	≥2.5	2.35	18.0	5.7	>19.0	>19.0	3.0
	8932144.001	Messer 3.0 T	≥3.0	2.85	18.0	5.7	>19.0	>19.0	2.5
	8932122.001	Messer 1.5 L	≥1.5	1.35	12.0	4.7	>15.0	>13.0	3.0
	8932123.001	Messer 2.0 L	≥2.0	1.85	12.0	5.2	>15.0	>13.0	3.0
	8932141.001	Messer 2.4 L	≥2.4	2.25	12.0	5.7	>15.0	>13.0	3.0
	8932124.001	Messer 2.5 L	≥2.5	2.35	12.0	5.7	>15.0	>13.0	3.0
	8932125.001	Messer 3.0 L	≥3.0	2.85	12.0	5.7	>15.0	>13.0	2.5
8932171.001 Matrix (as spare part)									

T-Blade With the T-blade off-cuts can be punched out right and left of the blade without turning the PCB. L-Blade




The L-blade will be used if there are small distances between the off-cuts




Matrix

Included in delivery.



Blades with varying thickness on request.





- Headquarters in Germany
- cab offices520 partnersin over 80 countries

cab maintains a presence in the world's major economic areas.



Germany

cab Produkttechnik GmbH & Co KG Postfach 1904 76007 Karlsruhe Wilhelm-Schickard-Str. 14 76131 Karlsruhe Telefon +49 721 6626-0 Telefax +49 721 6626-249 www.cab.de info@cab.de

Further partners on request.

France

cab technologies s.a.r.l. 67350 Niedermodern Téléphone +33 388 722 501 www.cab.de/fr info.fr@cab.de

USA

cab Technology Inc.
Tyngsboro MA, 01879
Phone +1 978 649 0293
www.cab.de/us
info.us@cab.de

Asia 亚洲

cab Technology Co, Ltd. **专定比科技股份有限公司** Junghe, Taipei, Taiwan Phone +886 2 8227 3966 www.cab.de/tw

China 中国

info.asia@cab.de

cab (Shanghai) Trading Co., Little (Lip) (Shanghai) Trading Co., Little (Sh

This documentation and any translations hereof are the property of cab GmbH & Co KG.

The replication, processing, reproduction or distribution in whole or in parts requires our prior written consent. © Copyright by cab/9008453.

All delivery, design and technical specifications are compiled to the best of our current knowledge and are subject to change without prior notice.